



SmartBright Slim Panel

RC091V LED36S/840 PSU W30L120 GM

SmartBright Slim Panel, 80 lm/W, 840 neutral white

SmartBright Slim Panel provides the most affordable LED solution to replace TL troffer. Its slim design (height of luminaire only 10mm) and multiple mounting options cater various applications (including plastic ceiling). As an edge light architecture, SlimBright Slim Panel delivers comfortable light with Excellent uniformity.

Product data

General Information		Operating and Electrical	
Light source replaceable	No	Light source color	840 neutral white
Number of gear units	1 unit	Optic type	Wide beam
Driver included	Yes	Luminaire light beam spread	120°
CE mark	CE mark	Input Voltage	220/240 V
Warranty period	3 years	Line Frequency	50 to 60 Hz
Flammability mark	-	Inrush current	8.1 A
ENEC mark	-	Inrush time	100 ms
Glow-wire test	Temperature 650 °C, duration 30 s	Power Consumption	45 W
EU RoHS compliant	No	Power Factor (Fraction)	0.9
Light Technical		Connection	Internal connector
Luminous Flux	3,600 lm	Cable	-
Correlated Color Temperature (Nom)	4000 K	Number of products on MCB of 16 A type B	50
Luminous Efficacy (rated) (Nom)	80 lm/W		
Color rendering index (CRI)	>80		
Beam angle of light source	- degree(s)		

SmartBright Slim Panel

Temperature

Ambient temperature range	-10 to +35 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	-
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Metal
Reflector material	-
Optic material	Polystyrene
Optical cover material	Polystyrene
Fixation material	Steel
Housing Color	White
Optical cover finish	Opal
Overall length	297 mm
Overall width	1,197 mm
Overall height	41 mm
Dimensions (Height x Width x Depth)	41 x 1197 x 297 mm

Approval and Application

Ingress protection code	IP20 [Finger-protected]
-------------------------	-------------------------

Mech. impact protection code	IK02 [0.2 J standard]
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.43, 0.40) SDCM>5
Power consumption tolerance	+/-10%

Application Conditions

Maximum dim level	Not applicable
-------------------	----------------

Product Data

Order product name	RC091V LED36S/840 PSU W30L120 GM
Full product name	RC091V LED36S/840 PSU W30L120 GM
Full product code	87101633131500
Order code	911401845997
Material Nr. (12NC)	911401845997
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8710163313115
Numerator - Packs per outer box	4
EAN/UPC - Case	8710163313115

Dimensional drawing

