



GreenVision Xceed Gen2

BRP382 LED193/NW 140W 220-240V DM PSR

GreenVision Xceed Gen2, 19300 lm, 140 W, 740 neutral white, Analog, Safety class I

Sustainability, citizen well being and connectivity are key players in the game of differentiation among cities all over the world. And a way of achieving this goals is lighting. Lighting up streets and roads enhance the comfort, security and overall safety of our rapidly growing urban environments. Our GreenVision Xceed Gen2 makes an affordable LED road lighting solution that ensures sufficient light on your roads & streets. The GreenVision Xceed Gen2 family from Signify provides your city with a flexible lighting system which can be deployed anywhere in urban spaces, highways and rural areas – our luminaires provide the optimal light for all application areas. And, GreenVision Xceed Gen2 is ready to be connected and work with smart city ecosystem. Our new GreenVision Xceed Gen2 range is enhanced to give city lighting departments even more control – to choose the right light

Product data

| General Information | |
|------------------------------------|---|
| Light source replaceable | No |
| Driver included | Yes |
| CE mark | CE mark |
| Warranty period | 3 years |
| Flammability mark | For mounting on normally flammable surfaces |
| Light Technical | |
| Luminous Flux | 19,300 lm |
| Correlated Color Temperature (Nom) | 4000 K |

| Luminous Efficacy (rated) (Nom) | 140 lm/W |
|---------------------------------|--------------------------------|
| Color rendering index (CRI) | >70 |
| Light source color | 740 neutral white |
| Optical cover type | Polycarbonate micro lens optic |
| Operating and Electrical | |
| Input Voltage | 220 to 240 V |
| Line Frequency | 50 or 60 Hz |
| Power Consumption | 140 W |
| Power Factor (Fraction) | 0.9 |

GreenVision Xceed Gen2

| | |
|------------|---|
| Connection | - |
| Cable | - |

Temperature

| | |
|---------------------------|---------------|
| Ambient temperature range | -40 to +50 °C |
|---------------------------|---------------|

Controls and Dimming

| | |
|-------------------------------|------------------------------|
| Dimmable | Yes |
| Driver/power unit/transformer | Power supply unit regulating |
| Control interface | Analog |
| Constant light output | No |

Mechanical and Housing

| | |
|-------------------------------------|---------------------|
| Housing Material | Aluminum die cast |
| Optic material | Polycarbonate |
| Optical cover material | Glass |
| Fixation material | Aluminum |
| Housing Color | Gray |
| Overall length | 499 mm |
| Overall width | 310 mm |
| Overall height | 138 mm |
| Effective projected area | 0.16 m ² |
| Dimensions (Height x Width x Depth) | 138 x 310 x 499 mm |

Approval and Application

| | |
|-------------------------|--|
| Ingress protection code | IP66 [Dust penetration-protected, jet-proof] |
|-------------------------|--|

| | |
|------------------------------|-----------------------------|
| Mech. impact protection code | IK08 [5 J vandal-protected] |
| Protection class IEC | Safety class I |

Initial Performance (IEC Compliant)

| | |
|-----------------------------|-----------------------|
| Luminous flux tolerance | +/-10% |
| Initial chromaticity | (0.43, 0.40) SDCM < 5 |
| Power consumption tolerance | +/-10% |

Over Time Performance (IEC Compliant)

| | |
|---------------------------|-----------------|
| Median useful life L70B50 | 100,000 hour(s) |
|---------------------------|-----------------|


Application Conditions

| | |
|-------------------|-----|
| Maximum dim level | 10% |
|-------------------|-----|

Product Data

| | |
|---------------------------------|---------------------------------------|
| Order product name | BRP382 LED193/NW 140W 220-240V DM PSR |
| Full product name | BRP382 LED193/NW 140W 220-240V DM PSR |
| Full product code | 872016972425900 |
| Order code | 911401875398 |
| Material Nr. (12NC) | 911401875398 |
| Numerator - Quantity Per Pack | 1 |
| EAN/UPC - Product/Case | 8720169724259 |
| Numerator - Packs per outer box | 1 |
| EAN/UPC - Case | 8720169724259 |

Dimensional drawing



GreenVision Xceed Gen2

