



CitySphere

BDP782 ECO30/830/GN PSDD II DM RB DGR DD

CITYSPHERE, LED EconomyLine 3000 lm, Distribution medium, DynaDimmer with fixed presets version 3, Diameter 90 mm, posttop decorative

At a time of rapidly changing social practices, every city is looking to be more attractive, welcoming, convenient and safe. CitySphere is a post-top ambiance LED luminaire designed to create a comfortable and pleasant atmosphere that puts the users of public spaces at ease. A slim, discreet presence during the day, it brings urban spaces to life at night. CitySphere delivers a visually comfortable volume of light and gives the city its own color signature. CitySphere comes with dedicated spigots, brackets and poles, enabling development planners, specifiers and decision makers to create a consistent urban identity and ambience.

Product data

General Information			
Lamp family code	ECO30 [LED EconomyLine 3000 lm]	might automatically dim down to protect components	
Light source replaceable	No	Light source engine type	LED
Number of gear units	2 units	Product family code	BDP782 [CITYSPHERE]
Driver included	Yes	Lighting Technology	LED
Photocell	-	Value ladder	Specification
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire	Embedded control	DynaDimmer with fixed presets version 3
		CE mark	Yes
		Warranty period	3 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		Glow-wire test	Temperature 650 °C, duration 5 s
		EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.03
Luminous Flux	2,400 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	75 lm/W
Color rendering index (CRI)	80
Light source color	830 warm white
Optical cover type	Polycarbonate bowl/cover UV-resistant
Luminaire light beam spread	148° x 88°
Optic type outdoor	Distribution medium

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	65 A
Inrush time	0.1 ms
Power Consumption	32 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable 7.0 m without plug
Number of products on MCB of 16 A type B	21

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit with DynaDimmer
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Dark gray
Mounting device	Diameter 90 mm, posttop decorative

Optical cover shape	Conical
Optical cover finish	Ribbed
Overall height	172 mm
Overall diameter	661 mm
Effective projected area	0.343 m²

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Philips standard surge protection level
Protection class IEC	Safety class II

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.410, 0.390) SDCM <3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 75000 h	7.5 %
Lumen maintenance at median useful life* 75000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BDP782 ECO30/830/GN PSDD II DM RB DGR DD
Full product name	BDP782 ECO30/830/GN PSDD II DM RB DGR DD
Full product code	871794317683000
Order code	912300022730
Material Nr. (12NC)	912300022730
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943176830
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943176830

Dimensional drawing

