



Quebec LED

BRP775 LED49-4S/740 PSD DW50 PGR BK D9

QUEBEC LED, LED module 4900 lm, 740 neutral white, Power supply unit with DALI interface, Safety class I, Distribution wide 50, Flat glass, Black, Philips standard surge protection level, Spigot for diameter 60 mm

Quebec LED is a stylish luminaire designed to brighten up residential streets and pathways, precincts, parks and other urban spaces. It incorporates an energy-efficient LED engine with high-performance optics, while at the same time retaining the character of the original Quebec fixture. It also offers a choice of bowl versions and mounting options. All these factors together make Quebec LED a versatile solution that can meet the needs of any project.

Product data

General Information			
Lamp family code	LED49 [LED module 4900 lm]	Light source engine type	LED
Light source replaceable	Yes	Service tag	Yes
Number of gear units	1 unit	Product family code	BRP775 [QUEBEC LED]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	Value ladder	Value
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	-
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes
		Serviceability class	Class A, luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge protection device, optics, front cover and mechanical parts

Quebec LED

Light Technical	
Upward light output ratio	0.03
Luminous Flux	4,018 lm
Standard tilt angle posttop	5°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	132 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	23° - 8° x 152°
Optic type outdoor	Distribution wide 50

Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	21 A
Inrush time	0.225 ms
Power Consumption	30.5 W
Power Factor (Fraction)	0.98
Connection	Plug-in connector 3-pole Wieland/Adels compatible and 2x 2-pole control signal for light regulation
Cable	-
Number of products on MCB of 16 A type B	26

Temperature	
Ambient temperature range	-40 to +50 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing	
Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Glass
Fixation material	Aluminum
Housing Color	Black

Mounting device	Spigot for diameter 60 mm
Optical cover shape	Flat
Optical cover finish	Silkscreen print gray
Overall height	388 mm
Overall diameter	478 mm
Effective projected area	0.1 m²

Approval and Application	
Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Philips standard surge protection level
Sustainability rating	-
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-7%
Initial chromaticity	(0.381, 0.379) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)	
Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	25%

Product Data	
Order product name	BRP775 LED49-4S/740 PSD DW50 PGR BK D9
Full product name	BRP775 LED49-4S/740 PSD DW50 PGR BK D9
Full product code	871869908991700
Order code	08991700
Material Nr. (12NC)	912300023481
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699089917
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699089917

Quebec LED

Dimensional drawing

