



# ClearFlood Large

## BVP651 LED600-4S/740 DW10 ALU PSU

ClearFlood large, LED module 60000 lm, LED, Power supply unit (On/Off), Distribution wide 10, Aluminum

ClearFlood Large is designed to meet the requirements of a wide range of floodlighting applications from parking lots to tennis courts. One of the key advantages of ClearFlood Large, is that you can choose the exact lumen rating that you need for your specific application. Because ClearFlood incorporates extremely high-efficiency optics and state-of-the-art LEDs, it is a highly competitive solution that offers an outstanding lux/euro ratio and instant energy savings. What's more, thanks to the wide choice of optics, you will always benefit from maximum coverage for your application. ClearFlood BVP651 is also easy to install – simply plug it in and select the option that best suits your needs.

### Product data

General Information			
Lamp family code	LED600 [LED module 60000 lm]	Light source engine type	LED
Light source replaceable	Yes	Service tag	Yes
Number of gear units	2 units	Product family code	BVP651 [ClearFlood large]
Driver included	Yes	Lighting Technology	LED
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	Value ladder	Specification
		CE mark	Yes
		Warranty period	5 years
		Flammability mark	For mounting on normally flammable surfaces
		ENEC mark	ENEC mark
		EU RoHS compliant	Yes
		Light Technical	
		Upward light output ratio	0
		Luminous Flux	50,000 lm

ClearFlood Large

Standard tilt angle posttop	0°
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color rendering index (CRI)	70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	52° – 7° x 151°
Optic type outdoor	Distribution wide 10

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	13 A
Inrush time	1.32 ms
Power Consumption	370 W
Power Factor (Fraction)	0.99
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	3

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Control interface	-
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	880 mm

Overall width	656 mm
Overall height	100 mm
Effective projected area	0.41 m²
Dimensions (Height x Width x Depth)	100 x 656 x 880 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Luminaire surge protection level until 4 kV differential mode and 4 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.005 %
Control gear failure rate at median useful life 100000 h	0.1 %
Lumen maintenance at median useful life* 100000 h	L96

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BVP651 LED600-4S/740 DW10 ALU PSU
Full product name	BVP651 LED600-4S/740 DW10 ALU PSU
Full product code	871869910799400
Order code	912300023755
Material Nr. (12NC)	912300023755
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699107994
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699107994

# ClearFlood Large

## Dimensional drawing

