



ClearFlood

BVP650 LED420-4S/740 OFA52 ALU PSU

ClearFlood, LED module 42000 lm, LED, Power supply unit (On/Off), Optiflux asymmetrical axis angle 52°, Aluminum

ClearFlood is a range of floodlights that enables you to choose the exact lumen rating that you need for your specific application. Designed around state-of-the-art LEDs and extremely high-efficiency optics, this very competitive solution offers an industry-leading lux per euro ratio and significant energy savings. The choice of different optics in the ClearFlood range opens new application possibilities for LEDs. ClearFlood BVP650 is also easy to install and to maintain.

Product data

General Information		Value ladder	Specification
Lamp family code	LED420 [LED module 42000 lm]	CE mark	Yes
Light source replaceable	Yes	Warranty period	5 years
Number of gear units	2 units	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	EU RoHS compliant	Yes
Light source engine type	LED	Light Technical	
Product family code	BVP650 [ClearFlood]	Upward light output ratio	0
Lighting Technology	LED	Luminous Flux	35,000 lm
		Standard tilt angle posttop	0°
		Standard tilt angle side entry	0°
		Correlated Color Temperature (Nom)	4000 K
		Luminous Efficacy (rated) (Nom)	133 lm/W
		Color rendering index (CRI)	70
		Light source color	740 neutral white
		Optical cover type	Flat glass

Luminaire light beam spread	39° - 11° x 98°
Optic type outdoor	Optiflux asymmetrical axis angle 52°

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	265 W
Power Factor (Fraction)	0.99
Connection	Connection unit 3-pole
Cable	-
Number of products on MCB of 16 A type B	4

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Acrylate
Optical cover material	Glass
Fixation material	Steel
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	529 mm
Overall width	580 mm
Overall height	95 mm
Effective projected area	0.26 m²

Dimensions (Height x Width x Depth)	95 x 580 x 529 mm
-------------------------------------	-------------------

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 8 kV common mode
Sustainability rating	Lighting for circularity
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/- 7%
Initial chromaticity	(0.380, 0.390) SDCM <5
Power consumption tolerance	+/- 10%
Init. Color Rendering Index Tolerance	+/- 2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L95

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BVP650 LED420-4S/740 OFA52 ALU PSU
Full product name	BVP650 LED420-4S/740 OFA52 ALU PSU
Full product code	871869912889000
Order code	912300023948
Material Nr. (12NC)	912300023948
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699128890
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699128890

Dimensional drawing



