



# TubePoint gen2

## BGP237 LED540-4S/740 DSM11 D9 MIO-CIO MB

TubePoint GEN2 Large, LED module 54000 lm, 740 neutral white, Power supply unit with DALI interface, Safety class I, Distribution symmetrical medium 11, Dark gray

Many tunnel authorities have outdated tunnel lighting installations that urgently need replacing, but have only a limited budget to achieve it. Philips TubePoint Gen2 is the perfect solution. It's the cost-effective solution that's the result of years of experience in tunnel lighting and underpass lighting, combined with the latest technologies developed by Philips. With its modular design and state-of-the-art LED architecture, TubePoint Gen2 is a versatile, cost-effective luminaire that meets the most stringent tunnel lighting requirements. Manufactured from the highest-quality components that are specifically designed for tunnels, these tunnel luminaires promise a long lifetime, great performance and low maintenance costs. The lighting efficiency and wide choice of optics means the number of luminaires required for an installation can be reduced significantly compared with conventional solutions. And a high lumen per watt ratio at system level improves the total cost of ownership. TubePoint Gen2 is part of the Philips TotalTunnel solution for complete tunnel lighting. A solution you can trust for versatile, high performance lighting in traffic tunnels.

### Product data

General Information		Product family code	BGP237 [TubePoint GEN2 Large]
Lamp family code	LED540 [LED module 54000 lm]	Lighting Technology	LED
Light source replaceable	Yes	Value ladder	Specification
Number of gear units	3 units	CE mark	Yes
Driver included	Yes	Warranty period	5 years
Light source engine type	LED	Flammability mark	For mounting on normally flammable surfaces
Service tag	Yes		

## TubePoint gen2

ENEC mark	ENEC mark
EU RoHS compliant	Yes

### Light Technical

Upward light output ratio	0
Luminous Flux	44,820 lm
Standard tilt angle posttop	-
Standard tilt angle side entry	0°
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	142 lm/W
Color rendering index (CRI)	>70
Light source color	740 neutral white
Optical cover type	Flat glass
Luminaire light beam spread	101° x 158°
Optic type outdoor	Distribution symmetrical medium 11

### Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 to 60 Hz
Inrush current	53 A
Inrush time	0.3 ms
Power Consumption	315 W
Power Factor (Fraction)	0.99
Connection	-
Cable	-
Number of products on MCB of 16 A type B	2

### Temperature

Ambient temperature range	-30 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum die cast
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Glass
Fixation material	Stainless steel
Housing Color	Dark gray
Mounting device	Mounting bracket
Optical cover shape	Flat
Optical cover finish	Clear

Overall length	1,090.6 mm
Overall width	485.5 mm
Overall height	89.5 mm
Effective projected area	0.53 m²
Dimensions (Height x Width x Depth)	90 x 486 x 1091 mm

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK09 [10 J]
Surge Protection (Common/Differential)	Luminaire surge protection level until 6 kV differential mode and 6 kV common mode
Protection class IEC	Safety class I

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.3818, 0.3796) SDCM<3
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Driver failure rate at 5000 h	0.5 %
Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L97

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

### Product Data

Order product name	BGP237 LED540-4S/740 DSM11 D9 MIO-CIO MB
Full product name	BGP237 LED540-4S/740 DSM11 D9 MIO-CIO MB
Full product code	871869948298500
Order code	912300024116
Material Nr. (12NC)	912300024116
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699482985
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699482985

## TubePoint gen2

### Dimensional drawing

