



OptiVision LED gen3

BVP527 2030/757 BV A35-WB D9 T25 100K

OPTIVISION LED GEN3 LARGE, LED module 204000 lm, 757 cool white, 230 to 400 V, Asymmetrical

The Philips OptiVision LED gen3 floodlighting system provides a complete lighting solution for the simplest to the most complex area and recreational sports lighting applications. The high-efficiency floodlight comes with a single-piece die cast housing, hosting 2 and 3 LED engines respectively, which also function with an external driver box – separate for use at a distance from the floodlight (BV), or pre-fixed onto the mounting bracket of the floodlight (HGB) for ease of installation and lower initial cost. It meets the highest performance standards, provides outstanding light, quality, uniformity and ensures safety and visual comfort. OptiVision LED offers new possibilities to reduce energy consumption and increase flexibility (instant start, programmable lighting levels) when used in conjunction with Interact Sports lighting management system, dedicatedly designed for recreational and training facilities. The floodlight is also compatible with other external control systems through DALI.

Product data

General Information	
Lamp family code	LED2040 [LED module 204000 lm]
Light source replaceable	Yes
Number of gear units	1 unit
Driver included	Yes
Remarks	* At higher ambient temperatures (greater than the luminaire ambient selected) the luminaire might automatically dim down to protect components
Light source engine type	LED
Service tag	Yes
Product family code	BVP527 [OPTIVISION LED GEN3 LARGE]

Lighting Technology	LED
CE mark	Yes
Warranty period	3 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
EU RoHS compliant	Yes
Light Technical	
Upward light output ratio	0
Luminous Flux	161,000 lm

OptiVision LED gen3

Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	5700 K
Luminous Efficacy (rated) (Nom)	114 lm/W
Color rendering index (CRI)	>70
Light source color	757 cool white
Optical cover type	Polycarbonate bowl/cover clear
Luminaire light beam spread	50° - 16° x 116°
Optic type outdoor	Asymmetrical

Operating and Electrical

Input Voltage	230 to 400 V
Line Frequency	50 to 60 Hz
Inrush current	20 A
Inrush time	0.160 ms
Power Consumption	1,415 W
Power Factor (Fraction)	0.95
Connection	Connection unit 5-pole
Cable	-
Number of products on MCB of 16 A type B	-

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Aluminum
Housing Color	Aluminum
Mounting device	Mounting bracket adjustable
Optical cover shape	Flat
Optical cover finish	Clear
Overall length	441 mm
Overall width	695 mm

Overall height	695 mm
Overall diameter	737 mm
Effective projected area	0.512 m ²
Dimensions (Height x Width x Depth)	695 x 695 x 441 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Surge Protection (Common/Differential)	Surge protection level until 10 kV differential mode
Protection class IEC	Safety class I

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.322, 0.335) SDCM<5
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%

Product Data

Order product name	BVP527 2030/757 BV A35-WB D9 T25 100K
Full product name	BVP527 2030/757 BV A35-WB D9 T25 100K
Full product code	871869986751500
Order code	86751500
Material Nr. (12NC)	912300024306
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718699867515
Numerator - Packs per outer box	1
EAN/UPC - Case	8718699867515

OptiVision LED gen3

Dimensional drawing

