



Stela+ gen2 Long, Square & Wide

BPP612 24x /WW PSU II SRN GR SRG10 60/76

STELA-WIDE GEN2, Power supply unit (On/Off), Standard road optic for S-class

In 2008 the arrival of the Stela family heralded a revolution in street lighting. In Stela + gen2 we are now presenting the next generation of LEDs and introducing programmable drivers. The REVOLED cooling and light distribution concept enables tremendous energy savings and a corresponding reduction in CO2 emissions, whilst meeting current lighting standards. Excellent thermal management of the LEDs ensures a very long lifetime, eliminating the need for lamp replacement. Higher flux per LED, flux tuning (using L-Tune) and the option of employing Constant Light Output (CLO) make it possible either to reduce the number of LEDs needed (lower cost per light point) or, when using the same number of LEDs as before, to reduce the power consumption (lower Total Cost of Ownership).

Product data

General Information		B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components	
Lamp family code	XP-G2 [LED XP-G2]		
Light source replaceable	No		
Number of gear units	1 unit		
Driver included	Yes		
Photocell	-		
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example		
		Light source engine type	LED
		Product family code	BPP612 [STELA-WIDE GEN2]
		Lighting Technology	LED
		Value ladder	Performance
		Embedded control	-
		CE mark	Yes

Stela+ gen2 Long, Square & Wide

Warranty period	5 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	Yes

Light Technical

Upward light output ratio	0.5
Luminous Flux	2,610 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	3000 K
Luminous Efficacy (rated) (Nom)	87 lm/W
Color rendering index (CRI)	≥80
Number of light sources	24
Light source color	830 warm white
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	99° x 156°
Optic type outdoor	Standard road optic for S-class

Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	80 A
Inrush time	150 ms
Power Consumption	30 W
Power Factor (Fraction)	0.9
Connection	Screw connection with pug and socket
Cable	-
Number of products on MCB of 16 A type B	8

Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

Controls and Dimming

Dimmable	No
Driver/power unit/transformer	Power supply unit (On/Off)
Constant light output	No

Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Polymethyl methacrylate
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 to 76 mm

Optical cover shape	Curved
Optical cover finish	Clear
Overall length	445 mm
Overall width	660 mm
Overall height	125 mm
Effective projected area	0.06 m²
Dimensions (Height x Width x Depth)	125 x 660 x 445 mm

Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-7%
Initial chromaticity	(0.330, 0.340) SDCM <7
Power consumption tolerance	+/-10%
Init. Color Rendering Index Tolerance	+/-2

Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

Application Conditions

Performance ambient temperature Tq	25 °C
------------------------------------	-------

Product Data

Order product name	BPP612 24x /WW PSU II SRN GR SRG10 60/76
Full product name	BPP612 24x /WW PSU II SRN GR SRG10 60/76
Full product code	871794323729600
Order code	912300026491
Material Nr. (12NC)	912300026491
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943237296
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943237296

Stela+ gen2 Long, Square & Wide

Dimensional drawing

