



# Stela+ gen2 Long, Square & Wide

**BPP612 GRN70/NW PSD SRN GR D9 SRG10 60/7**

STELA-WIDE GEN2, LED GreenLine 7000 lm, Power supply unit with DALI interface, Standard road optic for S-class

In 2008 the arrival of the Stela family heralded a revolution in street lighting. In Stela + gen2 we are now presenting the next generation of LEDs and introducing programmable drivers. The REVOLED cooling and light distribution concept enables tremendous energy savings and a corresponding reduction in CO2 emissions, whilst meeting current lighting standards. Excellent thermal management of the LEDs ensures a very long lifetime, eliminating the need for lamp replacement. Higher flux per LED, flux tuning (using L-Tune) and the option of employing Constant Light Output (CLO) make it possible either to reduce the number of LEDs needed (lower cost per light point) or, when using the same number of LEDs as before, to reduce the power consumption (lower Total Cost of Ownership).

## Product data

General Information		
Lamp family code	GRN70 [LED GreenLine 7000 lm]	
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
Photocell	-	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example	B10. Therefore, the median useful life (B50) value also represents the B10 value. * At extreme ambient temperatures the luminaire might automatically dim down to protect components
Light source engine type	LED	
Product family code	BPP612 [STELA-WIDE GEN2]	
Lighting Technology	LED	
Value ladder	Performance	
Embedded control	-	
CE mark	Yes	

## Stela+ gen2 Long, Square & Wide

Warranty period	5 years
Flammability mark	-
ENEC mark	-
EU RoHS compliant	Yes

### Light Technical

Upward light output ratio	0.5
Luminous Flux	6,300 lm
Standard tilt angle posttop	0°
Standard tilt angle side entry	-
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	111 lm/W
Color rendering index (CRI)	≥70
Number of light sources	52
Light source color	Neutral white
Optical cover type	Polymethyl methacrylate bowl/cover
Luminaire light beam spread	99° x 156°
Optic type outdoor	Standard road optic for S-class

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 to 60 Hz
Inrush current	125 A
Inrush time	115 ms
Power Consumption	57 W
Power Factor (Fraction)	0.94
Connection	Screw connection with pug and socket
Cable	-
Number of products on MCB of 16 A type B	1

### Temperature

Ambient temperature range	-40 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

### Mechanical and Housing

Housing Material	Aluminum
Reflector material	-
Optic material	Glass
Optical cover material	Polymethyl methacrylate
Fixation material	Aluminum
Housing Color	Grey
Mounting device	Spigot for diameter 60 to 76 mm

Optical cover shape	Curved
Optical cover finish	Clear
Overall length	445 mm
Overall width	660 mm
Overall height	125 mm
Effective projected area	0.06 m <sup>2</sup>
Dimensions (Height x Width x Depth)	125 x 660 x 445 mm

### Approval and Application

Ingress protection code	IP66 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK10 [20 J vandal-resistant]
Surge Protection (Common/Differential)	Luminaire surge protection level until 10 kV differential mode and 10 kV common mode
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-5%
Initial chromaticity	(0.380, 0.380) SDCM <7
Power consumption tolerance	+/-5%
Init. Color Rendering Index Tolerance	+/-2

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 100000 h	10 %
Lumen maintenance at median useful life* 100000 h	L80

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	25%

### Product Data

Order product name	BPP612 GRN70/NW PSD SRN GR D9 SRG10 60/7
Full product name	BPP612 GRN70/NW PSD SRN GR D9 SRG10 60/7
Full product code	871794325373900
Order code	912300026520
Material Nr. (12NC)	912300026520
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8717943253739
Numerator - Packs per outer box	1
EAN/UPC - Case	8717943253739

## Stela+ gen2 Long, Square & Wide

### Dimensional drawing

