



1010 Beacon

Beacon, Aluminum, 100W A19, Bronze, 120V

Beacon, Aluminum, 100W A19, Bronze, 120V

The Hadco 101 series Beacon is available in an all-aluminum, composite and cast bronze housing. It is line voltage luminaire featuring a fully gasketed borosilicate glass refractor lens. Lamping includes incandescent, CFL and HID.

Product data

General information	
Lamp Envelope Code	A-19
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	100

Product data	
Order product name	BEACON,BRZ,120V
EAN/UPC - Product	783352002266
Order code	1010-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400104302
Net Weight (Piece)	2.730 kg
Catalog Number	1010-H
Catalog Number Description	Beacon, Aluminum, 100W A19, Bronze, 120V