



1012 Beacon

COMPOSITE BEACON,120V,100W,A19

Beacon, Composite, 100W A19, Bronze, 120V

The Hadco 101 series Beacon is available in an all-aluminum, composite and cast bronze housing. It is line voltage luminaire featuring a fully gasketed borosilicate glass refractor lens. Lamping includes incandescent, CFL and HID.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100
Product Data	
Order product name	COMPOSITE BEACON,120V,100W,A19

EAN/UPC - Product	783352002280
Order code	H
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400104304
Net Weight (Piece)	0.010 kg
Commercial Code	1012-H
Catalog Number Description	Beacon, Composite, 100W A19, Bronze, 120V
Quick Ship	Service Smart (2 Days) USA