



1012 Beacon

Beacon, Composite, 100W A19, Bronze, 120V

Beacon, Composite, 100W A19, Bronze, 120V

The Hadco 101 series Beacon is available in an all-aluminum, composite and cast bronze housing. It is line voltage luminaire featuring a fully gasketed borosilicate glass refractor lens. Lamping includes incandescent, CFL and HID.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100

Product Data	
Order product name	Beacon, Composite, 100W A19, Bronze, 120V

EAN/UPC - Product	783352002280
Order code	1012-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400104304
Net Weight (Piece)	0.010 kg
Catalog Number	1012-H
Catalog Number Description	Beacon, Composite, 100W A19, Bronze, 120V