



BL5016 Micro Accent

BULLYTE,MICRO,W/STAKE

Accent, Aluminum Bullyte w/ Stake, Black, 50W MR16, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp; also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	50
Number of Lamps	1
Mounting	NPT/NPS

Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	50

Product Data	
Order product name	BULLYTE,MICRO,W/STAKE

EAN/UPC - Product	783352004154
Order code	BL5016-AS7
Local order code	.
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400118714
Net Weight (Piece)	0.010 kg
Commercial Code	BL5016-AS7
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Black, 50W MR16, 12V
Quick Ship	Service Smart (2 Days) USA