



# BL5016 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Black, 50W MR16, 12V

Accent, Aluminum Bullyte w/ Stake, Black, 50W MR16, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

## Product data

<b>General information</b>		<b>EAN/UPC - Product</b>		783352004154
Lamp Envelope Code	MR-16	<b>Order code</b>		BL5016-AS7
Lamp Source Code	Quartz	<b>Numerator - Quantity Per Pack</b>		1
Lamp Watts	50	<b>Numerator - Packs per outer box</b>		1
Number of Lamps	1	<b>Material Nr. (12NC)</b>		912400118714
Mounting	NPT/NPS	<b>Net Weight (Piece)</b>		0.010 kg
Lamp Included	No	<b>Catalog Number</b>		BL5016-AS7
<b>Operating and electrical</b>		<b>Catalog Number Description</b>		Accent, Aluminum Bullyte w/ Stake, Black, 50W MR16, 12V
Voltages	12 V			
Luminaire Input Watts	50			
<b>Product data</b>				
Order product name	BULLYTE,MICRO,W/STAKE			