



# BL5016 Micro Accent

BULLYTE,12V,7W,MR16,LED,STAKE

Accent, Aluminum Bullyte w/ Stake, Verde, 7W LED, Flood, 3000K, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp; also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

## Product data

General Information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Color Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	7
Initial Performance (IEC Compliant)	
Luminaire Lumens	600

Product Data	
Order product name	BULLYTE,12V,7W,MR16,LED,STAKE
EAN/UPC - Product	783352017116
Order code	BL5016-GS7LED7FLW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400118742
Net Weight (Piece)	0.010 kg
Commercial Code	BL5016-GS7LED7FLW
Catalog Number Description	Accent, Aluminum Bullyte w/ Stake, Verde, 7W LED, Flood, 3000K, 12V
Quick Ship	-