



BL5016 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Bronze, 50W MR16, 12V

Accent, Aluminum Bullyte w/ Stake, Bronze, 50W MR16, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General information	
Lamp Envelope Code	MR-16
Lamp Source Code	Quartz
Lamp Watts	50
Number of Lamps	1
Mounting	NPT/NPS
Lamp Included	No
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	50
Product data	
Order product name	MICRO BULLYTE,12V,W/STAKE

EAN/UPC – Product		783352004260
Order code		BL5016-HS7
Numerator – Quantity Per Pack		1
Numerator – Packs per outer box		1
Material Nr. (12NC)		912400118753
Net Weight (Piece)		0.001 kg
Catalog Number		BL5016-HS7
Catalog Number Description		Accent, Aluminum Bullyte w/ Stake, Bronze, 50W MR16, 12V