



BL5016 Micro Accent

BULLYTE,MICRO,W/STAKE & LAMP

Accent, Aluminum Bullyte w/ Stake & Lamp, Bronze, 50W MR16, 12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp; also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General Information		Order code	BL5016-HS7BAB
Lamp Source Code	Quartz	Local order code	.
Lamp Watts	50	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	NPT/NPS	Material Nr. (12NC)	912400118755
Operating and Electrical		Net Weight (Piece)	0.700 kg
Voltages	12 V	Commercial Code	BL5016-HS7BAB
Luminaire Input Watts	50	Catalog Number Description	Accent, Aluminum Bullyte w/ Stake & Lamp, Bronze, 50W MR16, 12V
Product Data		Quick Ship	Service Smart (2 Days) USA
Order product name	BULLYTE,MICRO,W/STAKE & LAMP		
EAN/UPC - Product	783352002150		