



BL5016 Micro Accent

Accent, Aluminum Bullyte w/ Stake & Lamp,
Bronze, 50W MR16, 12V

Accent, Aluminum Bullyte w/ Stake & Lamp, Bronze, 50W MR16,
12V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General information		EAN/UPC - Product		783352002150
Lamp Envelope Code	MR-16	Order code		BL5016-HS7BAB
Lamp Source Code	Quartz	Numerator - Quantity Per Pack		1
Lamp Watts	50	Numerator - Packs per outer box		1
Number of Lamps	1	Material Nr. (12NC)		912400118755
Mounting	NPT/NPS	Net Weight (Piece)		0.700 kg
Lamp Included	No	Catalog Number		BL5016-HS7BAB
Operating and electrical		Catalog Number Description		Accent, Aluminum Bullyte w/ Stake & Lamp, Bronze, 50W MR16, 12V
Voltages	12 V			
Luminaire Input Watts	50			
Product data				
Order product name	BULLYTE,MICRO,W/STAKE & LAMP			