



BL5016 Micro Accent

Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Narrow Flood, 3000K, 12V

Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Narrow Flood, 3000K, 12V - 100 lm/W

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	7
Number of Lamps	1
Colour Temperature	3000 K
CRI	80
Photometric Distribution Type	Medium
Mounting	NPT/NPS
Number Of Pieces	1
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	7
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	600
Efficacy	100 lm/W
Product data	
Order product name	BULLYTE,12V,7W,MR16,LED,STAKE
EAN/UPC - Product	783352017017
Order code	BL5016-HS7LED7NFW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400118765
Net Weight (Piece)	0.001 kg
Catalog Number	BL5016-HS7LED7NFW

BL5016 Micro Accent

Catalog Number	Description
	Accent, Aluminum Bullyte w/ Stake, Bronze, 7W LED, Narrow Flood, 3000K, 12V

