



# BL616 Micro Accent

Accent, Aluminum Bullyte w/ Stake & Lamp, Black, 20W MR16, 12V

Accent, Aluminum Bullyte w/ Stake & Lamp, Black, 20W MR16, 12V

The BL616 is made with die-cast aluminum and has a fully adjustable swivel arm with vibration-proof locking teeth. Available in low voltage incandescent and LED sources.

## Product data

<b>General information</b>		<b>EAN/UPC - Product</b>	783352004376
Lamp Envelope Code	MR-16	<b>Order code</b>	BL616-AS7BAB
Lamp Source Code	Quartz	<b>Numerator - Quantity Per Pack</b>	1
Lamp Watts	50	<b>Numerator - Packs per outer box</b>	1
Number of Lamps	1	<b>Material Nr. (12NC)</b>	912400118784
Mounting	NPT/NPS	<b>Net Weight (Piece)</b>	0.001 kg
Lamp Included	No	<b>Catalog Number</b>	BL616-AS7BAB
<b>Operating and electrical</b>		<b>Catalog Number Description</b>	Accent, Aluminum Bullyte w/ Stake & Lamp, Black, 20W MR16, 12V
Voltages	12 V		
Luminaire Input Watts	50		
<b>Product data</b>			
Order product name	BULLYTE,MICRO,W/STAKE & LAMP		