



BT5016 Micro Accent

BULLYTE,MICRO,120V,50W,MR16

Accent, Aluminum Bullyte w/ Integral Transformer, Bronze, 50W, MR16, 120V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp; also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

Product data

General Information		EAN/UPC - Product		783352005014
Lamp Source Code	Quartz	Order code		BT5016-H
Lamp Watts	50	Numerator - Quantity Per Pack		1
Number of Lamps	1	Numerator - Packs per outer box		1
Mounting	NPT/NPS	Material Nr. (12NC)		912400118943
		Net Weight (Piece)		0.520 kg
Operating and Electrical		Commercial Code		BT5016-H
Voltages	120 V	Catalog Number Description		Accent, Aluminum Bullyte w/ Integral Transformer, Bronze, 50W, MR16, 120V
Luminaire Input Watts	50	Quick Ship		Service Smart (2 Days) USA
Product Data				
Order product name	BULLYTE,MICRO,120V,50W,MR16			