



# BT5016 Micro Accent

Accent, Aluminum Bullyte w/ Integral Transformer, Bronze, 50W, MR16, 120V

Accent, Aluminum Bullyte w/ Integral Transformer, Bronze, 50W, MR16, 120V

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

## Product data

General information		EAN/UPC - Product	
Lamp Envelope Code	MR-16	Order code	BT5016-H
Lamp Source Code	Quartz	Numerator - Quantity Per Pack	1
Lamp Watts	50	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400118943
Mounting	NPT/NPS	Net Weight (Piece)	0.520 kg
Lamp Included	No	Catalog Number	BT5016-H
Operating and electrical		Catalog Number Description	Accent, Aluminum Bullyte w/ Integral Transformer, Bronze, 50W, MR16, 120V
Voltages	120 V		
Luminaire Input Watts	50		
Product data			
Order product name	BULLYTE,MICRO,120V,50W,MR16		