



# BT5016 Micro Accent

Accent, Aluminum Bullyte, Bronze, 7W LED, Flood, 3000K, 120V

Accent, Aluminum Bullyte, Bronze, 7W LED, Flood, 3000K, 120V  
- 100 lm/W

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

## Product data

| General information           |                   |
|-------------------------------|-------------------|
| Lamp Source Code              | LED               |
| Lamp Watts                    | 7                 |
| Number of Lamps               | 1                 |
| Colour Temperature            | 3000 K            |
| CRI                           | 80                |
| Photometric Distribution Type | Wide Flood        |
| Mounting                      | NPT/NPS           |
| Number Of Pieces              | 1                 |
| Operating and electrical      |                   |
| Voltages                      | 120 V             |
| Luminaire Input Watts         | 7                 |
| Conduit Connection            | 7/8 inch knockout |

| Mechanical and housing              |                   |
|-------------------------------------|-------------------|
| Enclosure                           | Metal and Plastic |
| Initial performance (IEC compliant) |                   |
| Luminaire Lumens                    | 600               |
| Efficacy                            | 100 lm/W          |
| Product data                        |                   |
| Order product name                  | BULLYTE,120V,LED  |
| EAN/UPC - Product                   | 783352017727      |
| Order code                          | BT5016-HLED7FLW   |
| Numerator - Quantity Per Pack       | 1                 |
| Numerator - Packs per outer box     | 1                 |
| Material Nr. (12NC)                 | 912400118945      |
| Net Weight (Piece)                  | 0.988 kg          |
| Catalog Number                      | BT5016-HLED7FLW   |

BT5016 Micro Accent

| Catalog Number | Description  |
|----------------|--|
|                | Accent, Aluminum Bullyte, Bronze, 7W LED, Flood, 3000K, 120V |

