



UW1250 Underwater Light

NAVAL BRASS CORD SEAL,MALE

Brass Cord Seal, Brass Friction Ring. 1/2" NPT for use with 16-3 STO-WA entry into junction box.

The Hadco Underwater luminaires include the UW1250 and UWL1075 fixtures that offer cast bronze construction with a pivoting base. Available in low and line voltage, these luminaires have a natural cast brass finish that will age nicely over time. Optics include a clear convex, tempered glass furnished with silicone O-ring for watertight seal.

Product data

General Information		Numerator - Quantity Per Pack 1	
Lamp Watts	50	Numerator - Packs per outer box 50	
Mounting	Underwater	Material Nr. (12NC)	912400120953
Operating and Electrical		Net Weight (Piece)	0.001 kg
Voltages	120 V	Commercial Code	CCH50
Product Data		Catalog Number Description	Brass Cord Seal, Brass Friction Ring. 1/2" NPT for use with 16-3 STO-WA entry into junction box.
Order product name	NAVAL BRASS CORD SEAL,MALE	Quick Ship	-
Order code	CCH50		