



DB14 Bollard

Bollard, Aluminum, Bronze, 100W INC, 120V, 14"

Bollard, Aluminum, Bronze, 100W INC, 120V, 14"

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General information	
Lamp Envelope Code	A-19
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	100

Product data	
Order product name	BLLD,14"RD TOP,120V,100W,A19
EAN/UPC - Product	783352014825
Order code	DB14-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121673
Net Weight (Piece)	7.050 kg
Catalog Number	DB14-H
Catalog Number Description	Bollard, Aluminum, Bronze, 100W INC, 120V, 14"