



DB14 Bollard

Bollard, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V, 14"

Bollard, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V, 14" - 100 lm/W

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General information	
Lamp Source Code	LED
Lamp Watts	9.5
Number of Lamps	1
Colour Temperature	2700 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	Ground / Floor
Number Of Pieces	1

Operating and electrical	
Voltages	120 V
Luminaire Input Watts	9.5 W
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic

Initial performance (IEC compliant)	
Luminaire Lumens	800
Efficacy	100 lm/W

Product data	
Order product name	BOLLARD,LED
Order code	DB14AA012LE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121675
Net Weight (Piece)	0.001 kg
Catalog Number	DB14AA012LE

DB14 Bollard

Catalog Number	Description
	Bollard, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V, 14"

