



# DB14 Bollard

## BOLLARD,LED

Bollard, Aluminum, Symmetric, Bronze, 9.5 LED, 2700K, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

### Product data

<b>General Information</b>		<b>Order code</b> DB14HA012LE	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Lamp Watts	9.5	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400121677
Color Temperature	2700K	Net Weight (Piece)	0.010 kg
Mounting	Ground / Floor	Commercial Code	DB14HA012LE
<b>Operating and Electrical</b>		Catalog Number Description	Bollard, Aluminum, Symmetric, Bronze, 9.5 LED, 2700K, 120V
Voltages	120 V	Quick Ship	-
Luminaire Input Watts	9.5		
<b>Product Data</b>			
Order product name	BOLLARD,LED		