



DB21 Bollard

BLLD,42W,PLT-42

Bollard, Aluminum, Black, 42W PLT, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information	
Lamp Source Code	Compact Fluorescent
Lamp Watts	42
Number of Lamps	1
Mounting	Ground / Floor
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	42

Product Data

Order product name	BLLD,42W,PLT-42
--------------------	-----------------

Order code	DB21AA042FE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121683
Net Weight (Piece)	0.010 kg
Commercial Code	DB21AA042FE
Catalog Number Description	Bollard, Aluminum, Black, 42W PLT, 120V
Quick Ship	-