



# DB21 Bollard

## BOLLARD,LED

Bollard, Aluminum, Symmetric, Bronze, 9.5W LED, 2700K, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

### Product data

General Information	
Lamp Source Code	LED
Lamp Watts	9.5
Number of Lamps	1
Color Temperature	2700K
Mounting	Ground / Floor

  

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	9.5

  

Product Data	
Order product name	BOLLARD,LED

  

Order code	DB21HA012LE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121688
Net Weight (Piece)	0.001 kg
Commercial Code	DB21HA012LE
Catalog Number Description	Bollard, Aluminum, Symmetric, Bronze, 9.5W LED, 2700K, 120V
Quick Ship	-