



DB21 Bollard

Bollard, Aluminum, Bronze, 50W MH, 120V

Bollard, Aluminum, Bronze, 50W MH, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		Order code	DB21HA050HE
Lamp Source Code	Metal Halide	Numerator - Quantity Per Pack	1
Lamp Watts	50	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400121692
Mounting	Ground / Floor	Net Weight (Piece)	0.010 kg
Operating and Electrical		Catalog Number	DB21HA050HE
Voltages	120 V	Catalog Number Description	Bollard, Aluminum, Bronze, 50W MH, 120V
Luminaire Input Watts	50		
Product Data			
Order product name	BLLD,50W MH		