



DB30 Bollard

N/S, BLLD,100W INC

Bollards, Aluminum, Black, 100W INC, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		EAN/UPC - Product	
Lamp Source Code	Incandescent	Order code	DB30-A
Lamp Watts	100	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400121701
Operating and Electrical		Net Weight (Piece)	3.060 kg
Voltages	120 V	Commercial Code	DB30-A
Luminaire Input Watts	100	Catalog Number Description	Bollards, Aluminum, Black, 100W INC, 120V
Product Data		Quick Ship	Service Smart (2 Days) USA
Order product name	N/S, BLLD,100W INC		