



DB30 Bollard

BLLD,30"RD TOP,120V,100W,A19

Bollards, Aluminum, Bronze, 100W INC, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	Ground / Floor

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100

Product Data	
Order product name	BLLD,30"RD TOP,120V,100W,A19

EAN/UPC - Product	783352014832
Order code	DB30-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121702
Net Weight (Piece)	0.001 kg
Commercial Code	DB30-H
Catalog Number Description	Bollards, Aluminum, Bronze, 100W INC, 120V
Quick Ship	Service Smart (2 Days) USA