



# DB30 Bollard

**Bollards, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V**

Bollards, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V – 100 lm/W

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

## Product data

General information	
Lamp Source Code	LED
Lamp Watts	9.5
Number of Lamps	1
Colour Temperature	2700 K
CRI	80
Photometric Distribution Type	General Diffuse
Mounting	Ground / Floor
Number Of Pieces	1
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	9.5
Conduit Connection	7/8 inch knockout

Mechanical and housing	
Enclosure	Metal and Plastic
Initial performance (IEC compliant)	
Luminaire Lumens	800
Efficacy	100 lm/W
Product data	
Order product name	BLLD, LED
EAN/UPC - Product	190096019700
Order code	DB30AA012LE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121711
Net Weight (Piece)	0.001 kg

# DB30 Bollard

Catalog Number	DB30AA012LE
Catalog Number Description	Bollards, Aluminum, Symmetric, Black, 9.5W LED, 2700K, 120V

