



DB30 Bollard

BLLD,70W MH

Bollards, Aluminum, Black, 70W MH, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		Order code	912400121717
Lamp Source Code	Metal Halide	Local order code	.
Lamp Watts	70	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	Ground / Floor	Material Nr. (12NC)	912400121717
Operating and Electrical		Net Weight (Piece)	5.560 kg
Voltages	120 V	Commercial Code	DB30AA070HE
Luminaire Input Watts	70	Catalog Number Description	Bollards, Aluminum, Black, 70W MH, 120V
Product Data		Quick Ship	-
Order product name	BLLD,70W MH		