



DB30 Bollard

Bollards, Aluminum, Black, 70W MH, 120V

Bollards, Aluminum, Black, 70W MH, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information	
Lamp Source Code	Metal Halide
Lamp Watts	70
Number of Lamps	1
Mounting	Ground / Floor

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	70

Product Data	
Order product name	BLLD,70W MH

Order code	DB30AA070HE
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121717
Net Weight (Piece)	5.560 kg
Catalog Number	DB30AA070HE
Catalog Number Description	Bollards, Aluminum, Black, 70W MH, 120V