



DB30 Bollard

BLLD,42W,CFL

Bollards, Aluminum, Bronze, 42W PLT, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Product data

General Information		Order code	DB30HA042FE
Lamp Source Code	Compact Fluorescent	Numerator - Quantity Per Pack	1
Lamp Watts	42	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400121727
Mounting	Ground / Floor	Net Weight (Piece)	4.320 kg
Operating and Electrical		Commercial Code	DB30HA042FE
Voltages	120 V	Catalog Number Description	Bollards, Aluminum, Bronze, 42W PLT, 120V
Luminaire Input Watts	42	Quick Ship	-
Product Data			
Order product name	BLLD,42W,CFL		