



# DB30 Bollard

BLLD,70W HPS

Bollards, Aluminum, Bronze, 70W HPS, 120V

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

## Product data

<b>General Information</b>		<b>EAN/UPC - Product</b>		783352022738
Lamp Source Code	High Pressure Sodium	Order code	912400121733	
Lamp Watts	70	Local order code	.	
Number of Lamps	1	Numerator - Quantity Per Pack	1	
Mounting	Ground / Floor	Numerator - Packs per outer box	1	
<b>Operating and Electrical</b>		Material Nr. (12NC)	912400121733	
Voltages	120 V	Net Weight (Piece)	0.010 kg	
Luminaire Input Watts	70	Commercial Code	DB30HA070SE	
<b>Product Data</b>		Catalog Number Description	Bollards, Aluminum, Bronze, 70W HPS, 120V	
Order product name	BLLD,70W HPS	Quick Ship	-	