



DWC1 Beacon

Beacon, Composite Semi Recessed, Black, 20W T3, 120V

Beacon, Composite Semi Recessed, Black, 20W T3, 120V

The DWC series is a low voltage beacon constructed of a single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. It is available in two distinctive heights. Composite is pressure formed, molded-in color. Optical assembly includes a borosilicate glass.

Product data

| General Information | |
|--------------------------|--------------------------------|
| Lamp Source Code | Quartz |
| Lamp Watts | 20 |
| Number of Lamps | 1 |
| Mounting | Ground / Floor |
| Operating and Electrical | |
| Voltages | 120 V |
| Luminaire Input Watts | 20 |
| Product Data | |
| Order product name | MINI BEACON,COMPOSITE,20W,120V |

| | |
|---------------------------------|---|
| EAN/UPC - Product | 783352006219 |
| Order code | DWC1-A |
| Numerator - Quantity Per Pack | 1 |
| Numerator - Packs per outer box | 1 |
| Material Nr. (12NC) | 912400121906 |
| Net Weight (Piece) | 0.001 kg |
| Catalog Number | DWC1-A |
| Catalog Number Description | Beacon, Composite Semi Recessed, Black, 20W T3, 120V |