



# DWC2 Beacon Series

## Beacon, Composite Semi Recessed, Black, 20W T3, 120V

Beacon, Composite Semi Recessed, Black, 20W T3, 120V

The DWC series is a low voltage beacon constructed of a single-piece compression molded fiberglass reinforced polyester composite, factory pressure tested to ensure water will not wick or leak through. It is available in two distinctive heights. Composite is pressure formed, molded-in color. Optical assembly includes a borosilicate glass.

### Product data

General information	
Lamp Envelope Code	T-3
Lamp Source Code	Quartz
Lamp Watts	20
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No
Operating and electrical	
Voltages	120 V
Luminaire Input Watts	20
Product data	
Order product name	SEMI-RECESSED,120V,20W,T3

EAN/UPC - Product	783352006226
Order code	DWC2-A
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121907
Net Weight (Piece)	0.001 kg
Catalog Number	DWC2-A
Catalog Number Description	Beacon, Composite Semi Recessed, Black, 20W T3, 120V