



DWCL2 Beacon

Beacon, Composite Semi Recessed, Black, 20W T3, 12V

Beacon, Composite Semi Recessed, Black, 20W T3, 12V

The DWCL series is a low voltage beacon constructed of a single-piece compression molded fiberglass reinforced polyester composite lower housing and die cast brass upper housing. It is available in two distinctive heights. The natural brass is as-cast and tumble polished. Composite is pressure formed, molded-in color. Optical assembly includes a borosilicate glass.

Product data

General information	
Lamp Envelope Code	T-3
Lamp Source Code	Quartz
Lamp Watts	20
Number of Lamps	1
Mounting	Ground / Floor
Lamp Included	No
Operating and electrical	
Voltages	12 V
Luminaire Input Watts	20
Product data	
Order product name	SEMI-RECESSED,12V,20W,T3

EAN/UPC - Product	783352006240
Order code	DWCL2-A
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400121909
Net Weight (Piece)	2.074 kg
Catalog Number	DWCL2-A
Catalog Number Description	Beacon, Composite Semi Recessed, Black, 20W T3, 12V