



i2 Inground

INGROUND 100W 120V R30

Inground w/ Bronze Trim Ring, Bronze, 100W R30, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100
Product Data	
Order product name	INGROUND 100W 120V R30

EAN/UPC - Product	783352006707
Order code	I2-H
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400122753
Net Weight (Piece)	0.001 kg
Commercial Code	I2-H
Catalog Number Description	Inground w/ Bronze Trim Ring, Bronze, 100W R30, 120V
Quick Ship	Service Smart (2 Days) USA