



# i2 Inground

## Inground w/ Cast Bronze Trim Ring, Natural Brass, 100W R30, 120V

Inground w/ Cast Bronze Trim Ring, Natural Brass, 100W R30, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

### Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100
Product Data	
Order product name	INGROUND,BRZ RING,100W,120V

EAN/UPC - Product	783352015617
Order code	I2-N
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400122754
Net Weight (Piece)	0.010 kg
Catalog Number	I2-N
Catalog Number Description	Inground w/ Cast Bronze Trim Ring, Natural Brass, 100W R30, 120V