



i2 Inground

Inground w/ Stainless Steel Trim Ring, Stainless Steel, 100W R30, 120V

Inground w/ Stainless Steel Trim Ring, Stainless Steel, 100W R30, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100
Product Data	
Order product name	SM INGR,SS TRIM RING, 100 INC

EAN/UPC - Product	783352021076
Order code	I2-SS
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (I2NC)	912400122755
Net Weight (Piece)	0.001 kg
Catalog Number	I2-SS
Catalog Number Description	Inground w/ Stainless Steel Trim Ring, Stainless Steel, 100W R30, 120V