



i25 Inground

Inground, 100W INC, Natural Brass, 120V

Inground, 100W INC, Natural Brass, 120V

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i2.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

Product data

General Information	
Lamp Source Code	Incandescent
Lamp Watts	100
Number of Lamps	1
Mounting	In Ground

Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	100

Product Data	
Order product name	I25 INGROUND,100W INCAND

Order code	I25-N
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (I2NC)	912400122756
Net Weight (Piece)	12.840 kg
Catalog Number	I25-N
Catalog Number Description	Inground, 100W INC, Natural Brass, 120V