



i25 Inground

I25 INGROUND,LED

Inground, 17W LED, Narrow Flood, Natural Brass, 3000K, 120V

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench - the i2.5 reinforces HADCO's position as the leader in landscape lighting. Now available with LED

Product data

General Information		Order code I25NNFW	
Lamp Source Code	LED	Numerator - Quantity Per Pack	1
Lamp Watts	17	Numerator - Packs per outer box	1
Number of Lamps	1	Material Nr. (12NC)	912400122780
Color Temperature	3000K	Net Weight (Piece)	15.090 kg
CRI	80	Commercial Code	I25NNFW
Mounting	In Ground	Catalog Number Description	Inground, 17W LED, Narrow Flood, Natural Brass, 3000K, 120V
Operating and Electrical		Quick Ship	-
Voltages	120 V		
Luminaire Input Watts	17		
Product Data			
Order product name	I25 INGROUND,LED		