



i25 Inground

Inground, 17W LED, Narrow Flood, Natural Brass, 3000K, 120V

Inground, 17W LED, Narrow Flood, Natural Brass, 3000K, 120V

The revolutionary i2.5 composite inground provides optimum performance in a small aperture luminaire. Patented design elements including a hinged lens ring, potted factory seal, cool lens option and only 2 screws that do not require a torque wrench – the i2.5 reinforces HADCO’s position as the leader in landscape lighting. Now available with LED

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	17
Number of Lamps	1
Colour Temperature	3000K
CRI	80
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	17

Product Data	
Order product name	I25 INGROUND,LED
Order code	I25NNFW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400122780
Net Weight (Piece)	15.090 kg
Catalog Number	I25NNFW
Catalog Number Description	Inground, 17W LED, Narrow Flood, Natural Brass, 3000K, 120V