



# IL Composite Inground

## Inground, Composite w/ Cast Bronze Trim Ring, Natural Brass, 75W MR16, 12V

Inground, Composite w/ Cast Bronze Trim Ring, Natural Brass, 75W MR16, 12V

The IL Composite Inground luminaire is for low voltage landscape lighting. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. It is available in halogen, incandescent and LED. The optical assembly has a clear convex, tempered soda-lime glass and 358° rotation without interruption of the beam pattern.

### Product data

General Information	
Lamp Source Code	Quartz
Lamp Watts	75
Number of Lamps	1
Mounting	In Ground
Operating and Electrical	
Voltages	12 V
Luminaire Input Watts	75
Product Data	
Order product name	INGROUND,CAST BRZ RING,12V

EAN/UPC - Product	783352021151
Order code	IL116- N
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400123056
Net Weight (Piece)	0.580 kg
Catalog Number	IL116- N
Catalog Number Description	Inground, Composite w/ Cast Bronze Trim Ring, Natural Brass, 75W MR16, 12V