



i2 Inground

Inground, Composite, Flood, Bronze, 7W LED, 2700K, 120V

Inground, Composite, Flood, Bronze, 7W LED, 2700K, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

Product data

General Information	
Lamp Source Code	LED
Lamp Watts	50
Colour Temperature	3000K
CRI	80
Photometric Distribution Type	Medium
Mounting	In Ground
Operating and Electrical	
Voltages	120 V
Luminaire Input Watts	50
Initial Performance (IEC Compliant)	
Luminaire Lumens	4500

Product Data	
Order product name	INGROUND,COMP RING,LED
EAN/UPC - Product	783352018571
Order code	IT216-HLED7FLW
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	1
Material Nr. (12NC)	912400123101
Net Weight (Piece)	2.168 kg
Catalog Number	IT216-HLED7FLW
Catalog Number Description	Inground, Composite, Flood, Bronze, 7W LED, 2700K, 120V