



# i2 Inground

## INGROUND CAST BRZ RING,12V

Inground, w/ Cast Bronze Trim Ring, Natural Brass, 75W MR16, 120V

The i2 Inground is a line voltage inground luminaire available in halogen, incandescent and LED sources. Its single-piece compression molded fiberglass reinforced polyester composite is factory pressure tested to ensure water will not wick or leak through. The optical assembly has a clear convex tempered soda-lime glass lens and 358° rotation without interruption of beam pattern.

### Product data

<b>General Information</b>		<b>Order code</b>	IT216-N
Lamp Source Code	Quartz	Local order code	-
Lamp Watts	75	Numerator - Quantity Per Pack	1
Number of Lamps	1	Numerator - Packs per outer box	1
Mounting	In Ground	Material Nr. (12NC)	912400123102
<b>Operating and Electrical</b>		Net Weight (Piece)	2.700 kg
Voltages	120 V	Commercial Code	IT216-N
Luminaire Input Watts	75	Catalog Number Description	Inground, w/ Cast Bronze Trim Ring, Natural Brass, 75W MR16, 120V
<b>Product Data</b>		Quick Ship	-
Order product name	INGROUND CAST BRZ RING,12V		
EAN/UPC - Product	783352021212		